



T 140

U out
500 V



18 AWG 0,5 - 1,0
mm²



0,6 - 1,0



Technology for Light

Lampholder 2G11

26.726.4808.50

DESCRIPTION

For cable insertion direction please refer to drawing

Product name:	Lampholder 2G11
Short description:	Supports for TC-L lamps
Mounting method 1:	Snap-in foot 25.5 x 13.3 mm
Material:	Housing: PBT
Wiring:	through snap in foot
Approval:	additional cULus
cULus file no.:	E-92235
Material thickness:	0.6 - 1.0
Color:	white
Weight:	14
Pkg.:	250