



# Mounting clip for vertical farming LED modules

## 37.132.-303.80



T 130

Tm 110

U out  
500 V



18 AWG 0,5 - 1,0  
mm<sup>2</sup>



0,4 - 2,0



# Mounting clip for vertical farming LED modules

## 37.132.-303.80



### DESCRIPTION

Screw fixing: Sheet metal screw St 4.2x12 or cylinder head screw M4x12 (max. head height 4 mm/1.16``)

Product name:	Mounting clip for vertical farming LED modules
Country of origin:	DE
Packaging quantity:	1.000
Mounting method 1:	Screw mount
Color:	black
Pkg.:	1