




NEW

MLF

FEATURES

- ※Horizontal operation
- ※Various LED colors
- ※Mid-mount type


APPLICATION

- ※Server, desktop
- ※Communication apparatus
- ※IPC

SPECIFICATION

Contact Rating	50mA, 12V DC
Contact Resistance	100mΩ max.
Insulation Resistance	10MΩ min. 100V DC
Dielectric Strength	250V AC/1 minute
Operating Force	200±70gf
Travel	1.5mm
Operating Life	100, 000 cycles
Operating Temp.	-40°C ~ +85°C
Storage Temp.	-40°C ~ +85°C

CIRCUIT



PACKAGE

<Tape & Reel>
570 pcs.

HOW TO ORDER

MLF - 3 **QR**

Operation Force:
200gf

Package:
Tape & Reel





Halogen Free

LED Color:
□=Without LED
AW=Amber/White

MLF

LED Color Options:

Part No.	Color	Dominant Wavelength λ_p Typ.(nm)	Luminous Intensity I_v (mcd)	Forward Voltage V_F (V)		View Angle $2\theta_{1/2}$ (Degree)
			Typ.	Typ.	Max.	
B	Blue	470	70	3.0	3.6	140°
PG	Pure Gree	520	160	3.2	3.6	
G	Yellow Green	570	30	2.0	2.3	
Y	Yellow	590	60	2.0	2.3	
A	Soft Orange	605	50	2.0	2.3	
R	Deep Red	640	25	2.0	2.3	
W	Cold White	X:0.30 / Y:0.30	350	3.0	3.6	



P.C.B. LAYOUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diptronics:

[MLF-3QR](#) [MLF-3AWQR](#) [ML9-M4RQR](#) [ML9-M4WQR](#) [ML9-M4OQR](#) [ML9-M4GQR](#)