

FEATURES

- ★Side actuation
- ☆Gold contact for high reliability
- *Red, blue, and black color options.


APPLICATION

- ★Industrial control
- *Computers and peripherals
- ★ Variety of function controls

SPECIFICATION

Con	tact Rating	25mA, 24V DC
Con Res	tact istance	50m $Ω$ max.
	llation istance	100M Ω min. 500V DC
	ectric ngth	500V AC/1 minute
Ope	rating Force	1,000gf max.
Trav	/el	2mm
Ope	rating Life	2, 000 cycles
Ope	rating Temp.	-40°C ~ +85°C
Stor	age Temp.	-40°C ~ +85°C

CIRCUIT




PACKAGE


	•	T	u	е	>


\1 ube/	
NDA-02: 73pcs	NDA-02T: 70 pcs
NDA-03: 52pcs	NDA-03T: 50 pcs
NDA-04: 40pcs	NDA-04T: 39 pcs
NDA-05: 33pcs	NDA-05T: 32 pcs
NDA-06: 28pcs	NDA-06T: 28 pcs
NDA-07: 24pcs	NDA-07T: 24 pcs
NDA-08: 21pcs	NDA-08T: 21 pcs
NDA-09: 19pcs	NDA-09T: 19 pcs
NDA-10: 17pcs	NDA-10T: 17 pcs
NDA-12: 14pcs	NDA-12T: 14 pcs


HOW TO ORDER




NDA







NO.OF POS.	DIM.A	DIM.B
2	6.44	2.54
3	8.98	5.08
4	11.52	7.62
5	14.06	10.16
6	16.60	12.70
7	19.14	15.24
8	21.68	17.78
9	24.22	20.32
10	26.76	22.86
12	31.84	27.94
	POS. 2 3 4 5 6 7 8 9 10	POS. DIM.A 2 6.44 3 8.98 4 11.52 5 14.06 6 16.60 7 19.14 8 21.68 9 24.22 10 26.76



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diptronics:

 NDA-05V
 NDA-09V
 NDA-10V
 NDA-08V
 NDA-12V
 NDA-02V
 NDA-03V
 NDA-07V
 NDA-04V
 NDA-06V
 NDA-07V
 NDA-03TV
 NDA-08TV
 NDA-09BTV
 NDA-09FTV
 NDA-09TV
 NDA-09TV