

FEATURES

- ※Vertical and right angel type
- ※Flush & raised actuator
- ※BCD; Hexadecimal


APPLICATION

- ※Building & home automation
- ※White goods
- ※Electronic instrument

SPECIFICATION

Contact Rating	25mA, 24V DC
Contact Resistance	100mΩ max.
Insulation Resistance	100MΩ min. 250V DC
Dielectric Strength	250V AC/1 minute
Operating Force	400gf·cm max.
Operating Life	20,000 Steps
Operating Temp.	-25°C ~ +80°C
Storage Temp.	-40°C ~ +85°C

HOW TO ORDER



PACKAGE

<Tube>

48 pcs


<Tape & Reel>

750 pcs (recessed actuator)


500 pcs (3.2mm actuator)

250 pcs (7.3mm actuator)

RH2




RH2AF-16R




RH2AF-16C

TYPE	POSITION		CODE			
	□□R	16C	1	2	4	8
10R	0	F	●	●	●	●
	1	E	○	●	●	●
	2	D	●	○	●	●
	3	C	○	○	●	●
	4	B	●	●	○	●
	5	A	○	●	○	●
	6	9	●	○	○	●
	7	8	○	○	○	●
	8	7	●	●	●	○
	9	6	○	●	●	○
16R,C	A	5	○	○	○	○
	B	4	○	○	●	○
	C	3	●	●	○	○
	D	2	○	●	○	○
	E	1	●	○	○	○
	F	0	○	○	○	○




P.C.B. LAYOUT




RM3



RM3AF-16R




RM3AF-16C




TYPE	POSITION	CODE			
		1	2	4	8
10R	0	F	●	●	●
	1	E	○	●	●
	2	D	●	○	●
	3	C	○	○	●
	4	B	●	●	○
	5	A	○	●	●
	6	9	●	○	○
	7	8	○	○	○
	8	7	●	●	○
	9	6	○	●	○
16R,C	A	5	●	○	○
	B	4	○	○	○
	C	3	●	●	○
	D	2	○	●	○
	E	1	●	○	○
	F	0	○	○	○


RV4





RV4AF-16R



RV4AF-16C




RV4AF-10R




TYPE	POSITION	CODE			
		1	2	4	8
10R	0	F	●	●	●
	1	E	○	●	●
	2	D	●	○	●
	3	C	○	○	●
	4	B	●	●	○
	5	A	○	●	●
	6	9	●	○	○
	7	8	○	○	○
	8	7	●	●	○
	9	6	○	●	○
16R,C	A	5	●	○	○
	B	4	○	○	○
	C	3	●	●	○
	D	2	○	●	○
	E	1	●	○	○
	F	0	○	○	○



RS2




RS2AF-16R



RS2AF-10R



		CODE				
TYPE	POSITION					
		1	2	4	8	
10R	0	●	●	●	●	
	1	○	●	●	●	
	2	●	○	●	●	
	3	○	○	●	●	
	4	●	●	○	●	
	5	○	●	○	●	
	6	●	○	○	●	
	7	○	○	○	●	
	8	●	●	●	○	
	9	○	○	●	○	
16R	A	●	○	●	○	
	B	○	○	●	○	
	C	●	●	○	○	
	D	○	●	○	○	
	E	●	○	○	○	
	F	○	○	○	○	



P.C.B. LAYOUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diptronics:

[RS3AF-10R-V-B](#) [RS3AF-16R-V-B](#) [RS3HAF-10R-V-B](#) [RS3HAF-16R-V-B](#) [RS3MAF-10R-V-B](#) [RS3MAF-16R-V-B](#)