**FEATURES**


- ※Low profile for space saving
- ※Gold contact for high reliability
- ※Top tape type for washing process

**APPLICATION**

- ※Industrial control
- ※Automatic machines control
- ※Telecommunication

**SPECIFICATION**

Contact Rating	25mA, 24V DC
Contact Resistance	50mΩ max.
Insulation Resistance	100MΩ min. 500V DC
Dielectric Strength	500V AC/1 minute
Operating Force	1,000gf max.
Travel	1mm
Operating Life	2,000 cycles
Operating Temp.	-20°C ~ +85°C
Storage Temp.	-40°C ~ +85°C

**CIRCUIT****PACKAGE****<Tube>**

DM(R), DJ(R):

01: 130 pcs 02: 76 pcs 03: 55 pcs 04: 42 pcs  
 05: 35 pcs 06: 28 pcs 07: 25 pcs 08: 22 pcs  
 09: 20 pcs 10: 18 pcs 12: 15 pcs

**<Tape & Reel>**

DM(R)-01: 800 pcs

DMR-02~DMR-12: 900 pcs



DM-(01)(05)(07): 800 pcs

DM-(02)(03)(04)(06)(08)(09)(10)(12): 700 pcs




DJR-(02)(03)(04)(08)(09)(10): 1000 pcs

**<Bag>**


DL(R): 1000 pcs

**HOW TO ORDER****DM(R)**

## DJ(R)






PART NO.	NO.OF POS.	DIM.A	DIM.B
DJ(R)-02	2	6.02	2.54
DJ(R)-03	3	8.56	5.08
DJ(R)-04	4	11.10	7.62
DJ(R)-05	5	13.64	10.16
DJ(R)-06	6	16.18	12.70
DJ(R)-07	7	18.72	15.24
DJ(R)-08	8	21.26	17.78
DJ(R)-09	9	23.80	20.32
DJ(R)-10	10	26.34	22.86
DJ(R)-12	12	31.42	27.94




P.C.B. LAYOUT

## DL(R)



PART NO.	NO.OF POS.	DIM.A	DIM.B
DL(R)-01	1	3.48	
DL(R)-02	2	6.02	2.54
DL(R)-03	3	8.56	5.08
DL(R)-04	4	11.10	7.62
DL(R)-05	5	13.64	10.16
DL(R)-06	6	16.18	12.70
DL(R)-07	7	18.72	15.24
DL(R)-08	8	21.26	17.78
DL(R)-09	9	23.80	20.32
DL(R)-10	10	26.34	22.86
DL(R)-12	12	31.42	27.94



P.C.B. LAYOUT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diptronics:

[DJR-02-T-V-T/R](#) [DJR-12-T-V-T/R](#)