




FEATURES

- ※6x6mm, surface mounting type
- ※Optional ground pin
- ※Reflow solderable


APPLICATION

- ※Audio, OA equipment
- ※Instrumentation, Communication
- ※White goods

SPECIFICATION

Contact Rating	50mA, 12V DC
Contact Resistance	100mΩ max.
Insulation Resistance	100MΩ min. 500V DC
Dielectric Strength	250V AC/1 minute
Operating Force	100±50gf, Black(K) 160±50gf, Brown(N) 260±50gf, Red(R) 320±80gf, Salmon(S) 520±130gf, Yellow(Y)
Travel	0.25mm
Operating Life	Phosphor Bronze Dome 50,000 cycles for 520/320gf 100,000 cycles for 260gf 200,000 cycles for 160/100gf Stainless Steel Dome 300,000 cycles for 520/320gf 500,000 cycles for 260gf 1,000,000 cycles for 160/100gf
Operating Temp.	-25°C ~ +70°C
Storage Temp.	-30°C ~ +80°C

HOW TO ORDER



PACKAGE

<Tube>

77 pcs


<Tape & Reel>

DTSM(G)(J)-61 / DTSMG-62:1000 pcs


DTS(M)(J)-62:900 pcs DTSM(G)(T)-63, 64:700 pcs DTSJ-65:400 pcs

DTSM(G)-65:380 pcs DTSM-68:300 pcs DTSM-66:200 pcs




CIRCUIT



DTSM-6




PART NO.	H
DTSM-61	4.30
DTSM-62	5.00
DTSM-63	7.00
DTSM-65	9.50
DTSM-66	13.00
DTSM-68	11.30






P.C.B. LAYOUT

DTSM-644(8)




PART NO.	□A	□B
DTSM-644	2.40	1.60
DTSM-648	2.80	2.00






P.C.B. LAYOUT

TACT SWITCH

DTSMG-6




PART NO.	H
DTSMG-61	4.30
DTSMG-62	5.00
DTSMG-63	7.00
DTSMG-65	9.50
DTSMG-66	13.00
DTSMG-68	11.30






P.C.B. LAYOUT

DTSJ-6



PART NO.	H
DTSJ-61	4.30
DTSJ-62	5.00
DTSJ-63	7.00
DTSJ-65	9.50
DTSJ-66	13.00
DTSJ-68	11.30



P.C.B. LAYOUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diptronics:

[DTSM-61R-V-T/R](#) [DTSM-66Y-V-T/R](#) [DTSM-62K-V-T/R](#) [DTSM-644K-V-T/R](#) [DTSM-65Y-V-B](#) [DTSM-66S-V-B](#) [DTSM-65K-V-T/R](#) [DTSM-65R-V-B](#) [DTSM-65R-V-T/R](#) [DTSM-61R-V-B](#) [DTSM-61S-V-T/R](#) [DTSM-68N-V-T/R](#) [DTSM-65Y-V-T/R](#) [DTSM-62S-V-T/R](#) [DTSM-62R-V-T/R](#) [DTSM-644Y-V-T/R](#) [DTSM-62Y-V-B](#) [DTSM-65S-V-B](#) [DTSM-63K-V-B](#) [DTSM-66S-V-T/R](#) [DTSM-644S-V-T/R](#) [DTSM-62R-V-B](#) [DTSM-66K-V-B](#) [DTSM-62K-V-B](#) [DTSM-644R-V-B](#) [DTSM-66N-V-T/R](#) [DTSM-66R-V-B](#) [DTSM-644K-V-B](#) [DTSM-644N-V-T/R](#) [DTSM-63K-V-T/R](#) [DTSM-63N-V-T/R](#) [DTSM-68K-V-T/R](#) [DTSM-68S-V-T/R](#) [DTSM-68Y-V-T/R](#) [DTSM-63S-V-T/R](#) [DTSM-65S-V-T/R](#) [DTSM-61Y-V-T/R](#) [DTSM-62Y-V-T/R](#) [DTSM-644R-V-T/R](#) [DTSM-63Y-V-B](#) [DTSM-62S-V-B](#) [DTSM-63R-V-B](#) [DTSM-61K-V-B](#) [DTSM-63Y-V-T/R](#) [DTSM-68R-V-T/R](#) [DTSM-61K-V-T/R](#) [DTSM-66K-V-T/R](#) [DTSM-61Y-V-B](#) [DTSM-63S-V-B](#) [DTSM-66R-V-T/R](#) [DTSM-61S-V-B](#) [DTSM-63R-V-T/R](#) [DTSM-644N-V-B](#) [DTSM-61N-V-B](#) [DTSM-66N-V-B](#) [DTSM-62N-V-B](#) [DTSM-62N-V-T/R](#) [DTSM-61N-V-T/R](#) [DTSM-65N-V-B](#) [DTSM-65N-V-T/R](#) [DTSM-65K-V-B](#) [DTSM-63N-V-B](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diptronics:](#)

[DTSM-648N-V-B](#)