










Nur rot gestempelte oder auf Laufkarte gedruckte Dokumente unterliegen dem Änderungsdienst und sind zur Fertigung freigegeben.
Only red stamped or on jobcard printed documents are managed. These documents are approved for production.

All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Creo Parametric

Additional coding
View in direction A
4:1



Technical information

- Solder contacts: AWG28
- Current load: 1A@140° (Single contact)
- Test voltage: 750V (acc. SAE AS 13441:1998, Contact to contact)
- Rated voltage: 250V (acc. SAE AS 13441:1998) 2)

- 1) ODU recommend an additional locking of the nut with adhesive (e.g. Loctite 2701) to the screw thread.
- 2) Maximal operating voltage at sea level up to 2.000m.
Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first.
This must be evaluated in the frame of equipment engineering.

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach
DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009
connectors without switching capacity (COC) !

				Benennung/description: Geraeteteil cpl. Receptacle		Werkstoff: material: see BOM	
Allgemeine toleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		A PERFECT ALLIANCE.		CAD-Nr.: design-ID: 00101798		Maßstab: scale: 5:1	
Status/state: Approved		Version: revision: -		Teile-ID: part-ID:		Format: size: A3	
Erstellt/prepared 15.01.2016		prock		Oxaion-Nr.:		Einheit: dim.: mm	
Geaendert/revised 15.01.2016		prock		GKOW _C -P16LBC 0-000L		BL.:	
Freigabe/released 29.01.2016		mmeier		Ursprung/origin.:		sheet: 1	
ODU-MUEHL DORF		Datum/date		Name/name			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU USA:

[GK0WBC-P16LBC0-000L](#)