


General information

|                   |                     |
|-------------------|---------------------|
| Part number       | GKCWAM-P02UC00-000L |
| Termination       | pcb                 |
| Size              | 00                  |
| Locking principle | break               |
| Keying            | a_key_amc           |
| Cable Diameter    | cable_amchd_C       |



Contact insert description

|                      |         |
|----------------------|---------|
| Number of contacts   | 2       |
| Contact type         | sockets |
| Contact diameter     | 05mm    |
| Insulator material   | peek    |
| Termination          | pcb     |
| Termination diameter | 03mm    |

reverse\_gender\_on\_request

Technical information

|                                |          |               |
|--------------------------------|----------|---------------|
| Nominal current single contact | 03_a     | iec_60512_5_2 |
| Nominal current insert         | 3 A      | vde_0298_4    |
| Test voltage                   | 12_kv_dc | eia_364_20f   |

safety\_text

Mechanical and environmental data

|                       |              |
|-----------------------|--------------|
| Degree of protection* | ipsk8_ip6k9k |
| Operating temperature | 51_125_c     |
| Mating cycles         | 5000         |

mated

Material and surface treatments

|         |               |
|---------|---------------|
| Housing | ruthenium     |
| Contact | cu_alloy_gold |

safety\_text\_2  
ul\_text  
illustrative\_text

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU:

[GKCWAM-P02UC00-000L](#)