

K32B0C-P16NFG0-6500

series_b, type_k3



General information

Part number	K32B0C-P16NFG0-6500
Termination	crimp
Size	2
Locking principle	break , push
Keying	0_key
Cable Diameter	cable_mini_65
Cable outlet	standard



CODING: 0°

POSITIONS: 16 Positions

DIMENSIONS:

Contact insert description

Number of contacts	16
Contact type	sockets
Contact diameter	07mm
Insulator material	peek
Wire cross section	22-26_awg
Termination	crimp

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	06_mm	10_mm
Nominal current single contact	075_a	iec_60512_5_2
Nominal current insert	3,75 A	vde_0298_4
Test voltage	09_kv_ac	sae_13441

safety_text

Mechanical and environmental data

Degree of protection*	ip68
Operating temperature	40_120_c
Mating cycles	5000

mated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2
ul_text
illustrative_text

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU:

[K32B0C-P16NFG0-6500](#)