




**MARKETING SALES DRAWING**

**DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING**  
**DIMENSIONS IN METRIC - [ ]**

Electrical Testing  
 per Tusonix standard  
 test plans and Mil-Std-202  
 Test Methods.



MAXIMUM TIGHTENING TORQUE - 8 IN. LBS.

NOTE:  
 1. SUPPLIED WITH SILVER HEX NUT AND LOCKWASHER.

TUSONIX STYLE	321-010
CAP. VALUE	1000 pF
CAP. TOL.	± 20 %
TEMP. COEF.	X5U
VOLT. RATING	500 VDC
OPERATING TEMP. RANGE	-55 TO +85°C

X-2015 Rev-0 <b>REVISION RECORD</b> Original Release C.O. 20010529-2-01 0	<b>--TOLERANCES--</b> Unless Otherwise Specified		Title <b>FEED-THRU CAPACITOR</b>		
	DECIMAL ±.015 [0.38]		Drawn L.E. 05-29-01	Scale 4 X	
	ANGLES ±		Approved B.Mc. 05-29-01		
	<b>TUSONIX</b> TUCSON, ARIZONA		<b>A</b>	<b>321-010-X5U0-102M</b>	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[0321-010-X5U0-102M](#)