



This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING DIMENSIONS IN METRIC - []



NOTES:

- SUPPLIED WITH SILVER PLATED HEX NUT.
- MOUNTING TORQUE NOT TO EXCEED 5 lb-in. [.565 Nm].
- TUSONIX STANDARD PART NUMBER: 2425-003-X7W0-502AA. TUSONIX RoHS COMPLIANT PART NUMBER: 2425-003-X7W0-502AA LF. CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- PART MARKING: STANDARD PART: BLACK INK FOR TRADEMARK AND CAP. CODE. RoHS PART: GREEN INK FOR TRADEMARK AND CAP. CODE.

SPECIFICATIONS

TUSONIX STYLE:	2425-000
CAP. VALUE:	5,000 pF
CAP. TOLERANCE:	GMV
TEMP. CHARACTERISTIC:	X7W
RATING:	200 VDC @ + 85°C/100 VDC @ + 125°C
OPERATING RANGE:	100 VDC @ + 125°C
IR MIN. @ 100 VDC:	10 G Ω
DWV VDC:	600

REVISION RECORD	Original Release	0	REVISED RATING, ADDED IR & DWV, ADDED & REVISED NOTES, S.M. 03-10-06	1	20060217-2-01	--TOLERANCES-- Unless Otherwise Specified	Title MINIATURE BUSHING FEED-THRU	
	C.O. 19990713-1-03					DECIMAL ± .031 [0.79]	Drawn S.M. 07-15-99	Scale 4 X
						ANGLES ±	Approved E.F. 07-15-99	
						TUSONIX TUCSON, ARIZONA	A 2425-003-X7W0-502AA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2425-003-X7W0-502AALF](#)