




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



SPECIFICATIONS

CAP. VALUE:	4700 pF
CAP. TOL.:	$\pm 20\%$
TEMP. CHAR.:	Z5U (+10°C TO +85°C)
RATING:	250 VAC @ 50/60 Hz
CURRENT (A)	20
I.R. MIN @ 500 VDC	10 G Ω
BREAK DOWN	2250 VDC, 1 MIN.

NOTES:

1. TUSONIX STANDARD PART NUMBER: 2450-602-Z5U0-472M.
TUSONIX RoHS COMPLIANT PART NUMBER:
2450-602-Z5U0-472M LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD FINISH: SILVER PLATED.
3. PART MARKING: 3 DIGIT CAPACITANCE CODE MARKED ON EPOXY; RoHS PART, ADDITIONAL GREEN INK DOT OPPOSITE 3 DOT COLOR CODE ON EPOXY.

X-2015 Rev-0

REVISION RECORD		Original Release C.O. 970627-3 CORRECT LEAD DIM., ADDED METRIC & RESCALE DWG. S.M. 04-05-01 20010405-1-02 REVISED SPECIFICATIONS & ADDED NOTE, S.M. 04-15-04 20040415-1-03 ADDED AND REVISED NOTES. S.M. 01-26-06 20060110-2-04			
0	1				
2	3				
		--TOLERANCES-- Unless Otherwise Specified	Title DISCOIDAL FEED-THRU		
		DECIMAL ± NOTED			
		ANGLES ± 	Drawn E.C. 6-30-97		Scale 3 X
		TUSONIX TUCSON, ARIZONA	Approved J. Mc. 6-30-97		
			A	2450-602-Z5U0-472M	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2450-602-Z5U0-472M](#)