




Electrical Testing  
per Tusonix standard  
test plans and Mil-Std-202  
Test Methods.

# MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING

DIMENSIONS IN METRIC - [ ]



## NOTES:

1. SUPPLIED WITH SILVER PLATED HEX NUT AND LOCKWASHER.
2. TUSONIX STANDARD PART NUMBER: 4201-006.  
TUSONIX RoHS COMPLIANT PART NUMBER: 4201-006 LF.  
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
3. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
4. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.  
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT (Idc)	DWV (VDC)	I.R. MIN. @ 100 VDC	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
	1500	200	100	15 A	400	10 G	5	38	63

REVISION RECORD	Original Release C.O. <b>3173</b>	0	RDN TO COMP FMT & ADDED METRIC. 02-11-02	20020213-3-02	1	ADDED NOTES. S.M. 07-27-05	20050726-2-15	2	--TOLERANCES-- Unless Otherwise Specified	Title <b>BUSHING STYLE EMI FILTER</b>
									DECIMAL ±	
									ANGLES ±	Drawn S.M. 01-11-02 Scale 4X
										Approved T.C. 02-11-02
X2015 Rev-0									A	<b>4201-006</b>

**TUSONIX**  
TUCSON, ARIZONA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

4201-006LF