





MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- SUPPLIED WITH SILVER PLATED HEX NUT AND LOCK WASHER.
- TUSONIX STANDARD PART NUMBER: 4202-051.
TUSONIX RoHS COMPLIANT PART NUMBER: 4202-051 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

MIN. CAP. (pF)	WORKING VOLTAGE (VDC)		CURRENT (Idc)	I.R. MIN. @ 100 (VDC.)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
5000	200	100	10 A	10 G	400	20	65	70	70

X-2015 Rev-0	REVISION RECORD				--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .031 [0.79] ANGLES ±  TUSONIX TUCSON, ARIZONA		Title				BUSHING STYLE EMI FILTER									
	Original Release C.O. 1653		CURRENT UNIT "A" ADDED. L.E. 8-20-85				2595		RDN TO COMP FMT & ADDED METRIC. 05-22-02		20020522-6-01		ADDED NOTES, IR & DWV. S.M. 05-19-05		20050503-6-26		Drawn S.M. 05-22-02		Scale 3 X	
																	Approved J.Mc. 05-22-02			
																	A		4202-051	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4202-051LF](#)