



Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4203-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4203-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCK WASHER.

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT IDC	I.R. MIN. @ 100 (VDC)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
1500	350	200	10 A	10 G Ω	700	5	45	70	70

X-2015 Rev-0	REVISION RECORD						TOLERANCES unless otherwise specified		Title BUSHING STYLE EMI FILTER	
	0		1		2		3			
	Original Release C.O.		WAS SK 6644-010-S. L.E. 01-13-84		DIM'S & TOL'S REV'D RELEASED. L.E. 1-8-85		1653			
			CURRENT UNIT "A" ADDED. L.E. 08-20-85		2595		RDN TO COMP FMT & ADDED METRIC. S.M. 05-22-02			
			20020522-6-02		ADDED NOTES, IR & DWV. S.M. 11-14-05		20051026-5-02			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4203-000LF](#)