




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

- TUSONIX STANDARD PART NUMBER: 4205-004.
TUSONIX RoHS COMPLIANT PART NUMBER: 4205-004 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED COPPER. RoHS PART #: SILVER PLATED COPPER.
- BUSHING: SILVER PLATED STEEL.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
- SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCK WASHER.
- MAXIMUM MOUNTING TORQUE 5 LB.-IN. [.565 N-m].

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT Idc	I.R. MIN. @ 100 (VDC)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			
	85° C	125° C				10 MHz	100 MHz	1 GHz	10 GHz
1500	250	125	15	10 G Ω	500	5	35	60	60

X-2015 Rev-0	REVISION RECORD			--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .031 [.79] ANGLES ± TUSONIX TUCSON, ARIZONA	Title BUSHING STYLE EMI FILTER		
	Original Release	0			Drawn	L.E. 11-28-00	Scale 6 X
	ADDED IR & DWV, ADDED & REVISED NOTES: S.M. 11-30-06				Approved	T.C. 11-28-00	
	20051102-4-04	1			A	4205-004	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4205-004](#)