



1		2		3		4		5		6		7		8		9		10	
B-FORMAT 2002		REVISONS		8		REDRAWN. ADDED PC LAYOUT, .020 & .170. .515±.010 WAS .578±.010, .300±.015 WAS .290±.015, .360±.010 WAS .385±.010, .500±.010 WAS .500, .241±.010 TRAVEL WAS .478±.010 TRAVEL & .075 WAS .070±.010. - .000		ADDED .300±.010. DGW 3-17-2004 Mar. 24, 2004											
														PDF File Made		CW INDUSTRIES Southampton, Pa. 18966		Title: SLIDE SWITCH RIGHT ANGLE D.P. 3 POS. W/SNAP-IN HOUSING	
																TOLERANCES UNLESS OTHERWISE SPECIFIED			
																2 Place Decimal ±.010 3 Place Decimal ±.005 Angles ..... ±1°		METRIC 1 Place Dec. ±.25mm 2 Place Dec. ±.13mm	
																Made for: CW IND.		Division:	
																Drawn by: DGW 3-17-2004		SWITCH	
																Checked by: GG 3-23-04			
																Approval: BF 3-23-4		Dwg. No. G-386-0001	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[G-386-0001](#)