

Rating	10A 125V, 6A 250V AC 1/2HP 125/250VAC	
	20A 14VDC, 10A 28VDC	
Contact Resistance	50m ohm Max.	
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temp.	- 25 ° C ~ 85 ° C	
Function	4P DPST (ON)-OFF	

()=Momentary Function

Material:

Frame: Black, Nylon 66 (94-V2)







Actuator: Black, PC (94-V2)

Terminals: Silver plated, Copper alloy

Waterproof Rubber: Black, Silicone

Printed: None

Waterproof: IP65



Full travel:4.5mm

RoHS Compliant

1 Added date code. 1/17/11.

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 12/15/10

Rev. 1

Unit: mm

Checked By: G.Guld

Title:
PUSH BUTTON SWITCH

CW P/N:
GPB527A202BB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GPB527A202BB](#)