









Rating	20A 12V DC	Mounting Hole			Circuit Diagram	
					ON	
Contact Resistance	50m ohm Max.				OFF	
Insulation Resistance	DC 500V 100M ohm Min.					
Dielectric Strength	AC 1000V 1 minute					
Operation Temperature	-25°c~85°c					
Switch Function	3P SPST ON-OFF(LED)	Thickness	X	Y		
		0.75....1.5	19.4-0.1	13+0.1		
		1.5....2.5	19.8-0.1	13+0.1		



Material:

Frame: Nylon 66 (94-V2), Black
 Actuator: PC clear (94-V2), Red
 Waterproof Rubber: Silicone, Black
 Terminals: Silver plated, Copper alloy
 Hot stamping: None
 Waterproof: IP65
 LED: Red



RoHS Compliant

CW INDUSTRIES
 Southampton, Pa. 18966
 Tel 215.355.7080/www.cwind.com

Date Drawn: 5/17/10

Rev. 0

Unit: mm

Checked By: GG

Title: **ROCKER SWITCH**

CW P/N: **GRB066B802BR1**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GRB066B802BR1](#)