

SPECIFICATIONS:

Rating: **25A 12V DC / 25A 125V AC**

Function: **ON - OFF - ON SPDT**

Pos 1 Pos 2 Pos 3

Contact Resistance: 20mΩ max. (initial)

Insulation Resistance: 100mΩ min. (at 500V DC)

Dielectric Strength: 1,500V AC 50/60 Hz for 1 minute
Temp. T55


Service Life: Mechanically: 100,000 operations min.

Electrically: 30,000 operations min.




Water Proof: IP68

Base Color- Gray

Actuator Color- Black



Panel Cutout



RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 3-19-12

Rev. 0

Unit: mm

Checked By: *G. Gold*

Title:
ROCKER SWITCH

CW P/N:
GRB134A2NABA1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GRB134A2NABA1](#)