






THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	18A 125VAC			<div>Mounting Hole</div> 		<div>Circuit Diagram</div>  <div>SPDT ON - OFF - ON</div>											
	10A 277VAC 3/HP																
	21A 14V DC																
Contact Resistance		50m ohm max.		<table><tr><th>Thickness</th><th>X</th><th>Y</th></tr><tr><td>0.75 - 1.25</td><td>21.2 + 0.1</td><td>36.6 + 0.1</td></tr><tr><td>1.25 - 2.00</td><td>21.2 + 0.1</td><td>36.8 + 0.1</td></tr><tr><td>2.00 - 3.00</td><td>21.2 + 0.1</td><td>37.0 + 0.1</td></tr></table>		Thickness	X	Y	0.75 - 1.25	21.2 + 0.1	36.6 + 0.1	1.25 - 2.00	21.2 + 0.1	36.8 + 0.1	2.00 - 3.00	21.2 + 0.1	37.0 + 0.1
Thickness	X	Y															
0.75 - 1.25	21.2 + 0.1	36.6 + 0.1															
1.25 - 2.00	21.2 + 0.1	36.8 + 0.1															
2.00 - 3.00	21.2 + 0.1	37.0 + 0.1															
Insulation Resistance		DC 500V 100M ohm min.															
Dielectric Strength		AC 1500V 1 minute															
Operating Temperature		-20 ^o C ~ 85 ^o C															

BASE COLOR: Black
BUTTON COLOR: Black



RoHS Compliant

 CW INDUSTRIES Southampton, Pa. 18966 Tel 215.355.7080/www.cwind.com	Date Drawn: 12/21/09	Rev. 0	Unit: mm	Checked By: G. Guld
	Title: ROCKER SWITCH	CW P/N: GRB263D001NNN		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GRB263D001NNN](#)