





Rating	20A 125VAC 3/4HP 125VAC		Mounting Hole	Circuit Diagram										
Contact Resistance	50m ohm Max.													
Insulation Resistance	DC 500V 100M ohm Min.													
Dielectric Strength	AC 1500V 1 minute													
Operation Temperature	-20°C~85°C													
Switch Function	3P SPDT ON-OFF-ON	<table><tr><td>Thickness</td><td>X</td><td>Y</td></tr><tr><td>0.75~1.25</td><td>21.2+0.1</td><td>36.6+0.1</td></tr><tr><td>1.25~2</td><td>21.2+0.1</td><td>36.8+0.1</td></tr><tr><td>2~3</td><td>21.2+0.1</td><td>37.0+0.1</td></tr></table>	Thickness	X	Y	0.75~1.25	21.2+0.1	36.6+0.1	1.25~2	21.2+0.1	36.8+0.1	2~3	21.2+0.1	37.0+0.1
Thickness	X	Y												
0.75~1.25	21.2+0.1	36.6+0.1												
1.25~2	21.2+0.1	36.8+0.1												
2~3	21.2+0.1	37.0+0.1												






Material:

Frame: Black, Nylon#66

Actuator: Black, Nylon#66+30%GF

Waterproof: IP66



RoHS Compliant

TOLERANCE: $\pm 0.3\text{mm}$ ($\pm 0.0012\text{inch}$) UNLESS OTHERWISE SPECIFIED.

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 3/12/09

Rev. 0

Unit: mm

Checked By: GG

Title: **ROCKER SWITCH**

CW P/N: **GRB271D1BBNN1NN**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GRB271D1BBNN1NN](#)