

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

E

D


C

B



A

B-FORMAT 2002

REVISIONS



OPTIONAL INSULATING BARRIERS



TERMINAL OPTIONS:

$.187''$ (4.75mm) x $.032''$ (.81mm) Solderless
 $.110''$ (2.79mm) x $.032''$ (.81mm) Solderless
 $.187''$ (4.75mm) x $.020''$ (.51mm) Solderless
 $.110''$ (2.79mm) wide with $.048''$ (1.22mm) x $.237''$ (6.02mm) Slot for Soldering


DIMENSIONS IN INCHES (MILLIMETERS)
DO NOT SCALE DRAWING

Dwg. No.

GRS-4022-XXXX

MOUNTING PANEL THICKNESS

Standard—.050" (1.27mm) to .150" (3.81mm).
Optional Mounting Claws for Custom Panel thickness are available.



TAB AND POLARIZATION OPTIONS

CW INDUSTRIES
Southampton, Pa. 18966

TOLERANCES UNLESS OTHERWISE SPECIFIED
2 Place Decimal $\pm .010$ METRIC
3 Place Decimal $\pm .005$ 1 Place Dec. $\pm .25$ mm
Angles $\pm 1^\circ$ 2 Place Dec. $\pm .13$ mm

Made for: CW IND.
Drawn by: DGW 10-28-2010
Checked by:
Approval:

Title: **ROCKER SWITCH ASSEMBLY**
D.P./D.T.

Division: **SWITCH**
Dwg. No. **GRS-4022-XXXX**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CW Industries:

[GRS-4022-0017](#) [GRS-4022-0014](#) [GRS-4022-0021](#) [GRS-4022-0002](#) [GRS-4022-0001](#) [GRS-4022-0003](#) [GRS-4022-0008](#)