



DIMENSIONS IN INCHES (MILLIMETERS)  
DO NOT SCALE DRAWING...

Drawing No.  
GRSV-4011-0011 THRU 0013

1 OF 2






### BACK PANEL PIERCING



### GLASS PANEL PIERCING

.172 - .202 PANEL THICKNESS  
(4.37 - 5.13)



PART NO.	MAT'L.	COLOR
-0011	VALOX	BLACK
-0012	VALOX	WT-1334
-0013	VALOX	ALMOND 50046

REVISIONS	DATE	BY	DESCRIPTION
RELEASED	12-28-93	DGW	
ADDED PAGE 2:	1-24-94	DGW	
.595 WAS .722 & .906 WAS .880 IN FRONT VIEW.	1-15-95	DGW	
ADDED ±.010 TO .630 IN FRONT VIEW.	1-29-98	DGW	
REMOVED BULB PAD PRINT & DIM'S .180 REF. & .162 REF. FROM TOP VIEW.	2-10-2005	DGW	
	FEB 11 2005		

**CW INDUSTRIES**  
Southampton, Pa. 18966

TOLERANCES UNLESS OTHERWISE SPECIFIED

2 Place decimal ±.010 METRIC  
3 Place decimal ±.005 1 Place dec. ± .25 MM  
Angles ± 1° 2 Place dec. ± 13 MM

Made for GE

Drawn by: DGW 12-28-93

Checked by: G. GULI 1-6-94

Approval: [Signature]

SWIDGET  
CUSTOM  
S.P.- S.T.

Division  
SWITCH



Drawing No.  
GRSV-4011-0011 THRU 0013

1 OF 2

DIMENSIONS IN INCHES (MILLIMETERS)  
DO NOT SCALE DRAWING....

Drawing No.  
GRSV-4011-0011 THRU 0013

2  
OF  
2



B-FORM-Q  
REVISIONS

RELEASED  
DWG 1-24-94

**CW INDUSTRIES**  
Southampton, Pa. 18966

Title

CLAW  
DETAILS

TOLERANCES UNLESS OTHERWISE SPECIFIED  
2 Place decimal ±.010 METRIC  
3 Place decimal ±.005 1 Place dec. ±.25 MM  
Angles ±1° 2 Place dec. ±13 MM

Made for GE

Division

SWITCH

Drawn by DWG 1-24-94

Drawing No.

GRSV-4011-0011 THRU 0013

2  
OF  
2

Checked by *[Signature]* 1/24/94

Approval *[Signature]* 1/24/94

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GRSV-4011-0011](#)