




THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating		16A. 12V DC		Mounting Hole		Circuit Diagram			
Contact Resistance		50m ohm max.							
Insulation Resistance		DC 500V 100M ohm min.							
Dielectric Strength		AC 1500V 1 minute							
Operating Temperature		-20°C ~ 85°C							
Switch Function		2P SPST ON-OFF LED Independent							
Lamp Type	LED Green @ 20mA, If=2.2VDC No Resistor								

Material:  
Frame: Black,Nylon#66  
Actuator: Black,Nylon#66  
LED Lens: Green PC  
LED:Green



Tolerances Unless Otherwise Specified +/- 0.3mm.

RoHS Compliant

4 Removed 20A rating, 12V sticker and 2P was 4P. Updated views. 1/5/15.

**CW INDUSTRIES**  
Southampton, Pa. 18966  
Tel 215.355.7080/www.cwind.com

Date Drawn: 12/17/09  
Rev. 4  
Title: **ROCKER SWITCH**

Unit: mm  
Checked By: *G. GOLD*  
CW P/N: **GRB066L02BBGGL1**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GRB066L02BBGGL1](#)