



SPECIFICATIONS:

Rating: DC30V 1A ;
 Contact resistance: 100m Ω (Max.) ;
 Insulation resistance: DC500V 100M Ω (Min.) ;
 Withstand voltage: AC 1000V for 1 minute ;
 Operating force: 700 \pm 150g ;
 Life cycle: 20,000 cycles ;
 Total Travel: 1.5 \pm 0.3 mm .

MATERIAL:

Frame:Nylon66,UL rated:94V-2 Min. ;
 Cap:POM ;
 Terminal:Brass,Silver or Tin plated .

Function:

ON(P-6)-OFF-ON (P-1)-OFF

Cap Color: Black

Order Chart

Series		Terminal Type	
GPTS202	31	2	B
Function		Button Color	

TS202-31-2-B

CW INDUSTRIES
 Southampton, Pa. 18966
 Tel 215.355.7080/www.cwind.com

Date Drawn: 12/21/17

Rev. 0

Unit: mm

Checked
 By: *OLF*

Title:

PUSH BUTTON SWITCH

CW P/N:

GPTS202312B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GPTS202312B](#)