
WRSP Series Weatherproof Single-pole Rocker Switches



UL recognized. CSA and VDE approvals pending. Load rating: 20A 125/250 VAC. 3/4 HP, 125/250 VAC. 14A 14VDC. Contacts: fine silver for long life dependability. Dielectric strength: 1250 volts (live parts to ground). Life: 35,000 operations at maximum rating. Insulation resistance: 5 megohms.

Water & Dust Resistance

Designed to meet IP-64.

High Inrush

125 Amp inrush capability (AgNi contacts).

Low Level Control

For low level/dry circuit applications (<100 am) contact factory for part number.

Terminals

Style A - 1/4-inch quick-connect

Mechanical Features

100,000 mechanical operations

Markings


Letters, numbers and symbols can be applied to rocker actuator or to integral nylon bezel; see inside back cover for details.


Mounting

Snap-in type panel mounting for ease of installation without additional mounting hardware.

| Circuit | Switching | | |
|---------|---|-------------------------|---------------|
| 1 | SPST Maintained | 2 1 OFF | 2 1 ON |
| 2 | SPDT Maintained | 2 1 3 ON | 2 1 3 ON |
| 3 | SPDT Maintained Center Off | 2 1 3 2 1 3 ON OFF | 2 1 3 ON |
| 4 | SPST (Momentary) Normally Open | 2 1 OFF | 2 1 (ON) |
| 5 | SPDT (Momentary) Normally Closed | 1 3 ON | 1 3 (OFF) |
| 6 | SPDT (Momentary) Transfer | 2 1 3 ON | 2 1 3 (ON) |
| 7 | SPDT Maintained Center Off (Momentary) | 2 1 3 2 1 3 ON OFF | 2 1 3 (ON) |
| 8 | SPDT (Momentary) Center Off (Momentary) | 2 1 3 2 1 3 (ON) OFF | 2 1 3 (ON) |











Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CW Industries:

<u>WRSP1A9M9</u> <u>WRSP3A9M9-G</u> <u>WRSP1A9M9-G</u> <u>WRSP1A9M9-G</u> <u>WRSP1A9M9-E</u> <u>WRSP3A9M9-E</u> <u>WRSP6A9M9E</u> <u>WRSP3H9M9</u> WRSP1A9M9-E WRSP1H9M9 WRSP4A9M9 WRSP1A9M9-WL WRSP2A9M9