


SLIDE SWITCHES (HALF PITCH) CHS


RoHS compliant



FEATURES

- RoHS compliant
- Meets EIAJ SOP standard outline dimensions (B type)
- Low profile design of 2.5 mm
- 12 types of 1, 2, 4, 6, 8 or 10 bit with either gull wing or J-hook available
- Excellent contact stability by twin Gold-plated contact
- Resin material is UL Recognized 94V-0

INTERNAL STRUCTURE



Part name		Material
①	Cover	Polyphenylenesulfide
②	Slider	Polyamide
③	Housing	Polyphenylenesulfide
④	Slider contact	Copper alloy, Gold-plated
⑤	Fixed contact	
⑥	Terminal pin	

PART NUMBER DESIGNATION

CHS		-	06	T	A	1	
Series name							Structure
No. of bits							1 : Non-washable type (Without seal tape) Standard type
01 : 1 bit							2 : Non-washable type (With seal tape)
02 : 2 bits							Blank : Washable type (With seal tape)
04 : 4 bits							
06 : 6 bits							
08 : 8 bits							
10 : 10 bits							
Form of packaging							Shape of terminal
T : Taping (Reel)							A : J-hook
M : Magazine							B : Gull wing
Blank : Bulk in plastic bag							

※ Please refer to the LIST OF PART NUMBERS when placing orders.

CHS

SLIDE SWITCHES (HALF PITCH)

LIST OF PART NUMBERS

No. of bits	Form of packaging	Shape of terminals	Non-washable type (Without seal tape)				Non-washable type (With seal tape)				Packaging quantity
			A	J-hook	B	Gull wing	A	J-hook	B	Gull wing	
1	Taping		CHS-01TA1		CHS-01TB1		CHS-01TA2		CHS-01TB2		1000 pcs./reel
	Magazine										
	Plastic bag		CHS-01A1		CHS-01B1						50 pcs./pack
2	Taping		CHS-02TA1		CHS-02TB1		CHS-02TA2		CHS-02TB2		500 pcs./reel
	Magazine										
	Plastic bag		CHS-02A1		CHS-02B1						50 pcs./pack
4	Taping		CHS-04TA1		CHS-04TB1		CHS-04TA2		CHS-04TB2		500 pcs./reel
	Magazine		CHS-04MA1		CHS-04MB1						70 pcs./stick
	Plastic bag		CHS-04A1		CHS-04B1						50 pcs./pack
6	Taping		CHS-06TA1		CHS-06TB1		CHS-06TA2		CHS-06TB2		500 pcs./reel
	Magazine		CHS-06MA1		CHS-06MB1						50 pcs./stick
	Plastic bag		CHS-06A1		CHS-06B1						50 pcs./pack
8	Taping		CHS-08TA1		CHS-08TB1		CHS-08TA2		CHS-08TB2		500 pcs./reel
	Magazine		CHS-08MA1		CHS-08MB1						40 pcs./stick
	Plastic bag		CHS-08A1		CHS-08B1						50 pcs./pack
10	Taping		CHS-10TA1		CHS-10TB1		CHS-10TA2		CHS-10TB2		500 pcs./ree
	Magazine		CHS-10MA1		CHS-10MB1						30 pcs./stick
	Plastic bag		CHS-10A1		CHS-10B1						50 pcs./pack

No. of bits	Form of packaging	Shape of terminals	Washable type (With seal tape)				Packaging quantity
			A	J-hook	B	Gull wing	
1	Taping		CHS-01TA		CHS-01TB		1000 pcs./reel
	Magazine						
	Plastic bag		CHS-01A		CHS-01B		50 pcs./pack
2	Taping		CHS-02TA		CHS-02TB		500 pcs./reel
	Magazine						
	Plastic bag		CHS-02A		CHS-02B		50 pcs./pack
4	Taping		CHS-04TA		CHS-04TB		500 pcs./reel
	Magazine		CHS-04MA		CHS-04MB		70 pcs./stick
	Plastic bag		CHS-04A		CHS-04B		50 pcs./pack
6	Taping		CHS-06TA		CHS-06TB		500 pcs./reel
	Magazine		CHS-06MA		CHS-06MB		50 pcs./stick
	Plastic bag		CHS-06A		CHS-06B		50 pcs./pack
8	Taping		CHS-08TA		CHS-08TB		500 pcs./reel
	Magazine		CHS-08MA		CHS-08MB		40 pcs./stick
	Plastic bag		CHS-08A		CHS-08B		50 pcs./pack
10	Taping		CHS-10TA		CHS-10TB		500 pcs./ree
	Magazine		CHS-10MA		CHS-10MB		30 pcs./stick
	Plastic bag		CHS-10A		CHS-10B		50 pcs./pack

☐ : Not manufactured

※ Verify the above part numbers when placing orders.

Taping and magazine version can be supplied only in reel or stick units.

CHS

SLIDE SWITCHES (HALF PITCH)

STANDARD SPECIFICATIONS

Operating temp. range	- 40 ~ 85 °C
Storage temp. range	
Sealing	Washable type available with seal tape
Net weight	Approx. 0.05 g (CHS-01) Approx. 0.08 g (CHS-02) Approx. 0.12 g (CHS-04) Approx. 0.17 g (CHS-06) Approx. 0.22 g (CHS-08) Approx. 0.25 g (CHS-10)

ELECTRICAL CHARACTERISTICS

Contact rating Non-switching Switching Minimum	DC50 V 100 mA DC6 V, 100 mA DC24 V, 25 mA DC20 mV 1 µA
Contact resistance	50 mΩ maximum
Insulation resistance	1000 MΩ (DC100 V) minimum
Dielectric strength	AC500 V, 60 s

MECHANICAL CHARACTERISTICS


Operating force	0.5 ~ 5 N {0.05 ~ 0.51 kgf}
Stop strength	10 N {1.02 kgf}, 60 s
Solderability	245 ± 3 °C, 2 ~ 3 s
Soldering heat	Reflow : 255 °C (Peak temperature) (Please refer to the profile below)
	Manual soldering : 350 ± 10 °C, 3 ~ 4 s
Shear (Adhesion)	5 N {0.51 kgf} 10 s
Substrate bending	Width 90 mm, bend 3 mm, 5 s, 1 time
Pull-off strength	5 N {0.51 kgf} 10 s

{ } : Reference only

ENVIRONMENTAL CHARACTERISTICS

Vibration	(Amplitude) 1.5 mm or (Acceleration) 98 m/s ² , 10-500 Hz, 3 directions for 10 cycles each
Shock	490 m/s ² , 11 ms 6 directions for 3 times each
Load life	Continuous load 2000 cycles, DC6 ± 0.5 V, 100 ± 10 mA
Humidity	-10 ~ 65 °C, Relative humidity 0 ~ 96 %, 24 h for 10 cycles
High temp. exposure	85 °C, 96 h
Low temp. exposure	-40 °C, 96 h
Thermal shock	-40 (0.5 h) ~ 85 °C (0.5 h), 5 cycles

<Reflow profile for soldering heat evaluation>




CHS

SLIDE SWITCHES (HALF PITCH)


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


CHS-01A1 Non-washable type (Without seal tape)



CHS-01B1 Non-washable type (Without seal tape)




CHS-02A1 Non-washable type (Without seal tape)



CHS-02B1 Non-washable type (Without seal tape)

(In accordance with EIAJ ED-7402-1)




CHS

SLIDE SWITCHES (HALF PITCH)


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


● CHS-04A1 Non-washable type (Without seal tape)




● CHS-04B1 (In accordance with EIAJ ED-7402-1) Non-washable type (Without seal tape)



● CHS-06A1 Non-washable type (Without seal tape)



● CHS-06B1 (In accordance with EIAJ ED-7402-1) Non-washable type (Without seal tape)




CHS

SLIDE SWITCHES (HALF PITCH)


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


CHS-08A1 Non-washable type (Without seal tape)




CHS-08B1 (In accordance with EIAJ ED-7402-1) Non-washable type (Without seal tape)



CHS-10A1 Non-washable type (Without seal tape)



CHS-10B1 (In accordance with EIAJ ED-7402-1) Non-washable type (Without seal tape)




CHS

SLIDE SWITCHES (HALF PITCH)


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


- **CHS-01A**
Washable type (With seal tape)
- **CHS-01TA2**
Non-washable type (With seal tape)




- **CHS-01B**
Washable type (With seal tape)
- **CHS-01TB2**
Non-washable type (With seal tape)



- **CHS-02A**
Washable type (With seal tape)
- **CHS-02TA2**
Non-washable type (With seal tape)



- **CHS-02B**
Washable type (With seal tape)
- **CHS-02TB2**
Non-washable type (With seal tape)



(In accordance with EIAJ ED-7402-1)


CHS

SLIDE SWITCHES (HALF PITCH)

OUTLINE DIMENSIONS


Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)

- **CHS-04A**
Washable type (With seal tape)
- **CHS-04TA2**
Non-washable type (With seal tape)




- **CHS-04B**
Washable type (With seal tape)
- **CHS-04TB2**
Non-washable type (With seal tape)

(In accordance with EIAJ ED-7402-1)




- **CHS-06A**
Washable type (With seal tape)
- **CHS-06TA2**
Non-washable type (With seal tape)



- **CHS-06B**
Washable type (With seal tape)
- **CHS-06TB2**
Non-washable type (With seal tape)

(In accordance with EIAJ ED-7402-1)



CHS


SLIDE SWITCHES (HALF PITCH)

OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)

- **CHS-08A**
Washable type (With seal tape)


- **CHS-08TA2**
Non-washable type (With seal tape)



- **CHS-08B**
Washable type (With seal tape)


- **CHS-08TB2**
Non-washable type (With seal tape)

(In accordance with EIAJ ED-7402-1)



- **CHS-10A**
Washable type (With seal tape)


- **CHS-10TA2**
Non-washable type (With seal tape)



- **CHS-10B**
Washable type (With seal tape)

- **CHS-10TB2**
Non-washable type (With seal tape)

(In accordance with EIAJ ED-7402-1)



CHS



SLIDE SWITCHES (HALF PITCH)

OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)

< Reference > The D version with opposite pin direction is available upon receipt of your order.

CHS-08D




RECOMMENDED P.C.B. PAD OUTLINE DIMENSIONS


1 bit

(Unit : mm)

A type




B type




2 bits

A type



B type




Note) The zero point is the center of mounting.

RECOMMENDED P.C.B. PAD OUTLINE DIMENSIONS


4 bits

(Unit : mm)

A type




B type




6 bits

A type




B type




8 bits

A type




B type




10 bits

A type



B type



Note) The zero point is the center of mounting.

CHS

SLIDE SWITCHES (HALF PITCH)

PACKAGING SPECIFICATIONS


<Taping packaging specifications>

- Taping version (CHS-02 ~ 10 types) are packaged in 500 pcs. per reel. Orders will be accepted for units of 500 pcs., i.e., 500, 1000, 1500 pcs., etc.
CHS-01 type is packaged in 1000 pcs. per reel. Orders will be accepted for units of 1000 pcs., i.e., 2000, 3000 pcs., etc.
- Taping version is boxed with two reels.

Maximum number of consecutive missing pieces=2

Leader length and reel dimension are shown in the diagrams below:


● Embossed tape dimensions




● Reel dimensions

(Conforms to JIS C 0806-3)
(In accordance with EIAJ ET-7200A)

(Unit: mm)




● 1 bit





(Conforms to JIS C 0806)

(Unit : mm)




● 2 bits



CHS


SLIDE SWITCHES (HALF PITCH)

4 bits





(Conforms to JIS C 0806)



(Unit : mm)





6 bits



8 bits



10 bits



CHS

SLIDE SWITCHES (HALF PITCH)


<Magazine packaging specifications>

- Packing quantities of magazines are different depending on the bit number of the switches.
Please order the multiple numbers of the specific packing quantities. (e.g. 70 pcs., 140 pcs., 210 pcs., etc., in case of 4 bits version)

Pieces in package : 4 bits, 70pcs./stick
6 bits, 50pcs./stick
8 bits, 40pcs./stick
10 bits, 30pcs./stick

● Magazine dimensions

(Unit : mm)



※ The magazine is common to A and B terminal pin.
Magazine length : 500 ± 2 mm long

<Bulk pack specifications>

- The smallest unit of bulk pack in a plastic bag is 10 pcs. per pack.
Orders will be accepted for unit of minimum 10 pcs., i.e., 10, 20, 30 pcs., etc.
- Boxing of bulk in a plastic bag is performed with 50 pcs. (standard 200 pcs.) per box.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Nidec:](#)

[CHS-04MA](#) [CHS-04MA1](#) [CHS-04MB](#) [CHS-04MB1](#) [CHS-06MA](#) [CHS-06MA1](#) [CHS-06MB](#) [CHS-06MB1](#) [CHS-08MA](#)
[CHS-08MA1](#) [CHS-08MB](#) [CHS-10MA](#) [CHS-10MA1](#) [CHS-10MB](#) [CHS-10MB1](#)