


SLIDE SWITCHES (SMD)

CMS


RoHS compliant



FEATURES

- RoHS compliant
- Excellent contact stability by twin Gold-plated contact mechanism
- Load life of 30,000 cycles
- Compatible with automatic mounting
- Withstands high soldering temperature
- Resin material is UL Recognized 94V-0

INTERNAL STRUCTURE



Part name	Material
① Cover	Steel (SPCC), Tin-plated
② Slider	Polyamide
③ Housing	
④ Slider contact	
⑤ Fixed contact	Copper alloy, Gold-plated
⑥ Terminal pin	
⑦ Click spring	Copper alloy
⑧ Ground terminal	Steel (SPCC), Tin-plated

PART NUMBER DESIGNATION

Series name	CMS	-	2	2	0	2	T	B	Shape of terminal
No. of poles									A : J-hook B : Gull wing C : Through hole pins
No. of contacts									Form of packaging
2 : 2 contacts 3 : 3 contacts 4 : 4 contacts									T : Taping (Reel) W : Tray packaging (Through hole pins only) Blank : Bulk in plastic bag
Setting position									Knob length
0 : Top setting 1 : Side setting									2 : 2 mm 4 : 4 mm (2 poles · Side setting only) 6 : 6 mm (4 poles · Side setting only)

※ Please refer to the LIST OF PART NUMBERS when placing orders.

LIST OF PART NUMBERS

● 2 poles

Setting position	Shape of terminals	Knob length	Form of packaging	No. of contacts			Packaging quantity
				2	3	4	
Top setting	A (J-hook)	2 mm	Taping	CMS-2202TA	CMS-2302TA	CMS-2402TA	900 pcs./reel
			Plastic bag	CMS-2202A	CMS-2302A	CMS-2402A	50 pcs./pack
	B (Gull wing)		Taping	CMS-2202TB	CMS-2302TB	CMS-2402TB	900 pcs./reel
			Plastic bag	CMS-2202B	CMS-2302B	CMS-2402B	50 pcs./pack
	C (Through hole pins)		Tray packaging	CMS-2202WC	CMS-2302WC	CMS-2402WC	50 pcs./tray
			Plastic bag	CMS-2202C	CMS-2302C	CMS-2402C	50 pcs./pack
Side setting	A (J-hook)	2 mm	Taping	CMS-2212TA	CMS-2312TA	CMS-2412TA	900 pcs./reel
			Plastic bag	CMS-2212A	CMS-2312A	CMS-2412A	50 pcs./pack
		4 mm	Taping	CMS-2214TA	CMS-2314TA	CMS-2414TA	900 pcs./reel
			Plastic bag	CMS-2214A	CMS-2314A	CMS-2414A	50 pcs./pack
	B (Gull wing)	2 mm	Taping	CMS-2212TB	CMS-2312TB	CMS-2412TB	900 pcs./reel
			Plastic bag	CMS-2212B	CMS-2312B	CMS-2412B	50 pcs./pack
		4 mm	Taping	CMS-2214TB	CMS-2314TB	CMS-2414TB	900 pcs./reel
			Plastic bag	CMS-2214B	CMS-2314B	CMS-2414B	50 pcs./pack
	C (Through hole pins)	2 mm	Tray packaging	CMS-2212WC	CMS-2312WC	CMS-2412WC	50 pcs./tray
			Plastic bag	CMS-2212C	CMS-2312C	CMS-2412C	50 pcs./pack
		4 mm	Tray packaging	CMS-2214WC	CMS-2314WC	CMS-2414WC	50 pcs./tray
			Plastic bag	CMS-2214C	CMS-2314C	CMS-2414C	50 pcs./pack

● 4 poles

Setting position	Shape of terminals	Knob length	Form of packaging	No. of contacts	Packaging quantity
				2	
Top setting	A (J-hook)	2 mm	Taping	CMS-4202TA	500 pcs./reel
			Plastic bag	CMS-4202A	25 pcs./pack
	B (Gull wing)		Taping	CMS-4202TB	500 pcs./reel
			Plastic bag	CMS-4202B	25 pcs./pack
	C (Through hole pins)		Plastic bag	CMS-4202WC	50 pcs./tray
			Tray packaging	CMS-4202C	25 pcs./pack
Side setting	A (J-hook)	6 mm	Plastic bag	CMS-4216TA	500 pcs./reel
			Taping	CMS-4216A	25 pcs./pack
	B (Gull wing)		Plastic bag	CMS-4216TB	500 pcs./reel
			Taping	CMS-4216B	25 pcs./pack
	C (Through hole pins)		Plastic bag	CMS-4216WC	50 pcs./tray
			Tray packaging	CMS-4216C	25 pcs./pack

※ Verify the above part numbers when placing orders.
Taping and tray version can be supplied only in reel or tray unit.

CMS

SLIDE SWITCHES (SMD)

STANDARD SPECIFICATIONS

Operating temp. range	- 40 ~ 85 °C	
Storage temp. range		
Sealing	Non- Washable	
Net weight	0.40 g (CMS-2202) 0.45 g (CMS-2302) 0.50 g (CMS-2402) 0.42 g (CMS-2212) 0.48 g (CMS-2312) 0.54 g (CMS-2412)	0.42 g (CMS-2214) 0.48 g (CMS-2314) 0.54 g (CMS-2414) 0.80 g (CMS-4202) 0.84 g (CMS-4216)

ELECTRICAL CHARACTERISTICS

Contact rating Non-switching Switching Minimum	DC50 V 100 mA DC12 V 100 mA DC20 mV 1 µA
Contact timing	Non-shorting
Contact resistance	70 mΩ maximum
Insulation resistance	100 MΩ minimum (DC500 V)
Dielectric strength	AC500 V, 60 s

MECHANICAL CHARACTERISTICS


No. of positions	2, 3, 4
Stroke	2 mm
Operating force	1.5 ± 1 N {0.15 ± 0.1 kgf}
Stop strength	30N{3.06 kgf} 15 s (Top setting) 10N{1.02 kgf} 15 s (Side setting)
Solderability	245 ± 3 °C 2 ~ 3 s
Soldering heat	Reflow : 255 °C (Peak temperature) (Please refer to the profile below)
	Flow : 260±3 °C、5 ~ 6 s
	Manual soldering : 350 ± 10 °C, 3 ~ 4 s
Shear (Adhesion)	50 N {5.09 kgf} 10 s
Substrate bending	Width 90 mm, bend 3 mm, 5 s, 1 time
Pull-off strength	50 N {5.09 kgf} 10 s

{ } : Reference only

ENVIRONMENTAL CHARACTERISTICS

Vibration	(Amplitude) 1.5 mm or (Acceleration) 98 m/s ² , 10-500-10 Hz, 3 directions for 10 cycles each
Shock	490 m/s ² , 11 ms, sinusoidal wave half cycle, 6 directions for 3 times each
Load life	Continuous load 30000 cycles, DC12 ± 0.5 V, 100 ± 10 mA
Humidity	40 °C, Relative humidity 90 ~ 95 %, 240 h, No load
High temp. exposure	85 °C, 96 h, No load
Low temp. exposure	-40 °C, 96 h, No load
Thermal shock	-40 (0.5 h) ~ 85 °C (0.5 h), 5 cycles

〈Reflow profile for soldering heat evaluation〉




CMS

SLIDE SWITCHES (SMD)


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


● CMS-2202A




● CMS-2202B




● CMS-2202C




● CMS-2212A




● CMS-2212B




● CMS-2212C



● CMS-2214A



● CMS-2214B




CMS

SLIDE SWITCHES (SMD)


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


● CMS-2214C




● CMS-2302A




● CMS-2302B




● CMS-2302C




● CMS-2312A




● CMS-2312B



● CMS-2312C



● CMS-2314A




CMS

SLIDE SWITCHES (SMD)


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


● CMS-2314B




● CMS-2314C




● CMS-2402A




● CMS-2402B




● CMS-2402C




● CMS-2412A



● CMS-2412B



● CMS-2412C




CMS

SLIDE SWITCHES (SMD)


OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


● CMS-2414A




● CMS-2414B




● CMS-2414C




● CMS-4202A




● CMS-4202B




● CMS-4202C



● CMS-4216A



● CMS-4216B




CMS

SLIDE SWITCHES (SMD)

OUTLINE DIMENSIONS

Unless otherwise specified, tolerance : ± 0.3 (Unit : mm)


● CMS-4216C




SIZE OF P.C.B. PROCESSING

(Unit : mm)


● CMS-22□□C




● CMS-23□□C



● CMS-24□□C




● CMS-42□□C



SLIDE SWITCHES (SMD)


RECOMMENDED P.C.B. PAD OUTLINE DIMENSIONS

● CMS-22□□A




● CMS-22□□B


(Unit : mm)




● CMS-23□□A




● CMS-23□□B




● **CMS-24□□A**




● **CMS-24□□B**



● CMS-42□□A



● **CMS-42□□B**



Note) The zero point is the center of mounting.


PACKAGING SPECIFICATIONS

<Taping packaging specifications>

- CMS-2□□□□ type is packaged in 900 pcs. per reel.
Orders will be accepted for units of 900 pcs., i.e., 900, 1800, 2700 pcs., etc. CMS-4 type is packaged in packaged in 500 pcs. per reel.
Orders will be accepted for units of 500 pcs.
- Taping version is boxed with one reel.


Maximum number of consecutive missing pieces=2
Leader length and reel dimension are shown in the diagrams below:

● Embossed tape dimensions




● Reel dimensions

(Unit: mm)
(Conforms to JIS C 0806)
(In accordance with EIAJ ET-7200A)



● CMS-2202TA, TB

(Unit : mm)
(Conforms to JIS C 0806)




CMS

SLIDE SWITCHES (SMD)


● CMS-2302TA, TB

(Conforms to JIS C 0806)




● CMS-2402TA, TB

(Unit : mm)
(Conforms to JIS C 0806)




● CMS-2212 • 2214TA, TB

(Conforms to JIS C 0806)




● CMS-2312 • 2314TA, TB

(Conforms to JIS C 0806)




● CMS-2412 • 2414TA, TB

(Conforms to JIS C 0806)




● CMS-4202TA, TB

(Conforms to JIS C 0806)



● CMS-4216TA, TB

(Unit : mm)
(Conforms to JIS C 0806)



<Tray packaging specifications>

- Tray version is packaged in 50 pcs. per tray. Orders will be accepted for units of 50 pcs., i. e., 50, 100, 150 pcs. etc.
- Tray version is boxed with 10 trays.

<Bulk pack specifications>

- The smallest unit of bulk pack in a plastic bag is 10 pcs. per pack.
Orders will be accepted for unit of minimum 10 pcs., i.e., 10, 20, 30 pcs., etc.
- Boxing of bulk in plastic bag is performed with 50 pcs. (standard 100 pcs. / CMS-2□□□□, 50 pcs. / CMS-4□□□□) per box.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Nidec:](#)

[CMS-2202WC](#) [CMS-2212WC](#) [CMS-2214WC](#) [CMS-2302WC](#) [CMS-2312WC](#) [CMS-2314WC](#) [CMS-2402WC](#) [CMS-](#)
[2412WC](#) [CMS-2414WC](#) [CMS-4202WC](#) [CMS-4216WC](#)