



© 2024 PennEngineering

ALL DIMENSIONS IN INCHES

DATE 18-MAR-2024

NOTE : DRAWING NOT TO SCALE

THREAD : .086-56 (#2-56)

MATERIAL: 300 Series Stainless Steel

HEAT TREAT: NONE

FINISH: Passivated and/or tested per ASTM A360

MOUNTING HOLE DIA. : .188 +.003 -.000

PANEL THICKNESS: .130 MINIMUM

MAX. PANEL HARDNESS: HRB 70 / HB 125 OR LESS

MIN CENTERLINE-TO-EDGE: 0.151

DESCRIPTION :

PEM® CASTSERT™ Press-in Inserts - Unified

PART NO. :

CKS-256-1



PennEngineering®

EMAIL: TECHSUPPORT@PEMNET.COM

WWW.PEMNET.COM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PEM:](#)

[CKS-256-1](#)