



© 2024 PennEngineering

ALL DIMENSIONS IN INCHES

DATE 18-MAR-2024

NOTE : DRAWING NOT TO SCALE

THREAD : .138-32 (#6-32)	MOUNTING HOLE DIA. : .250 +.003 -.000
MATERIAL: 300 Series Stainless Steel	PANEL THICKNESS: .205 MINIMUM
HEAT TREAT: NONE	MAX. PANEL HARDNESS: HRB 70 / HB 125 OR LESS
FINISH: Passivated and/or tested per ASTM A360	MIN CENTERLINE-TO-EDGE: 0.198
DESCRIPTION : PEM® CASTSERT™ Press-in Inserts - Unified	<div data-bbox="859 1968 980 2098" data-label="Image"> </div> <div data-bbox="995 1989 1549 2078" data-label="Text"> <p>PennEngineering®</p> </div> <div data-bbox="962 2130 1464 2197" data-label="Text"> <p>EMAIL: TECHSUPPORT@PEMNET.COM WWW.PEMNET.COM</p> </div>
PART NO. : CKS-632-1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PEM:](#)

[CKS-632-1](#)