



Notes

1. SMA Female Bulkhead Straight
 2. open ended coax
 3. Heatshrink
 - 4 Overall length 200mm
- Attenuation (Max) : -1.5dB
VSWR (Max) : 1.5
Nominal Impedance: 50ohm
RoHS compliant

All Dimensions in mm



**NOT TO
SCALE**

DESCRIPTION				
Cable Assy SMA(F) Bulkhead to Open Ended cable Assy 200mm				
FILENAME	DRAWN BY	DATE	REVISED	PAGE
CBA-SMAF-OP-1.VSD	John Fairall		30/05/2012	1 of 1
REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
N/A	1	First Issue	1.8.09	
	2			
	3			
	4			
	5			
	6			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RF Solutions:](#)

[CBA-SMAF-OP](#)