

Scotch® Filament Tape 8981



Technical Data

June, 2009

Product Description

Scotch® Filament Tape 8981 is a high-performance packaging tape reinforced with continuous glass-yarn filaments that give the tape very high tensile strength and low stretch. The clear 3M™ Scotchpro™ backing provides excellent abrasion and moisture resistance. The aggressive packaging-grade adhesive is specifically formulated to provide an excellent balance of initial adhesion and long-term holding power to most fiberboard surfaces, including recycled and printed fiberboard surfaces.

Construction

Backing	Adhesive	Reinforcement	Backing Color
3M™ Scotchpro™ film	Pressure sensitive synthetic rubber resin	Glass yarn	Clear

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.

ASTM Test Method		
Adhesion to Steel:	70 oz./in. width (77 N/100 mm width)	D-3330
Tensile Strength:	380 lbs./in. width (6655 N/100 mm width)	D-3759
Elongation at Break:	3%	D-3759
Total Thickness:	6.6 mil (0.168 mm)	D-3652

Features

- Meets ASTM D5330, Type II, which has replaced PPP-T-97E and CID A-A-1686A.
- Good handling.
- Printable.
- High tensile strength combined with low stretch.
- Allows printing and illustrations to be seen through the tape.
- High shear and good initial adhesion.
- Very good long-term holding power.
- Tough film backing protects the filaments and adhesive to provide longer functional tape performance.
- Good handling characteristics, saves time through ease of dispensing and tape application.
- When printed, the tape provides advertising, warning, and labeling capability.
- High tensile strength allows the use of less tape in many applications and lowers the cost per application.
- Good clarity of artwork and important messages even when covered by the tape.
- Adhesive provides very good holding under wide range of application conditions with minimum amount of tape.
- Holds instantly with minimum rubdown.
- Boxes remain securely closed through normal warehouse time cycles.

Scotch® Filament Tape

8981

Available Sizes	Available Widths	Available Lengths
	Standard Widths: .47 in. (12 mm), .71 in. (18 mm), .94 in. (24 mm), 1.4 in. (36 mm), 1.9 in. (48 mm)	60 yds. (55 m)
	.47 in. (12 mm), .71 in. (18 mm)	361 yds. (330 m)
	Core Size (ID): 3 in. (76.2 mm)	

Application Techniques	An extensive line of application equipment including hand-held manual dispensers and the 3M-Matic™ Semi-Automatic L-Clip Applicator S857 is available. Application of Scotch® Filament Tape 8981 is most easily accomplished at room temperature because at colder temperatures, approaching 32°F (0°C), the adhesive becomes firmer. Once applied, Scotch® Tape 8981 performs well throughout the normal temperature ranges typically encountered by packaged products in shipping and storage environments.
-------------------------------	---

Storage Conditions	Store behind present stock. Store in a clean, dry place. Temperature of 40-80°F (4-26°C) and 40-50% relative humidity are recommended. Rotate your stock.
---------------------------	---

Shelf Life	To obtain best performance, use this product within 18 months from date of manufacture.
-------------------	---

Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
------------------------------	--

Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.
--------------------	--

Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
---	---

Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.
--------------------------------	--

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

Scotch is a registered trademark of 3M.
3M, Scotchpro and 3M-Matic are
trademarks of 3M.
Printed in U.S.A.
©3M 2009 70-0710-0287-0 (6/09)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Corning:

8981-8882/HIGHGEL