

# 3M Scotch® Vinyl Mastic Tape

3M™ Scotch® Vinyl Mastic Tape is a rubber based mastic laminated to an all-weather 7 mil (0.18 mm) vinyl, which provides double duty protection in one wrap. Vinyl Mastic (VM) tape seals out moisture and protects against corrosion without the need for heating tools or using multiple tapes. VM tape is two tapes in one (vinyl and mastic) and specifically designed for cable sheath repair, splice case and load coil case protection, auxiliary sleeve and cable reel end sealing, drop wire insulating, conduit repair and protection of CATV components as well as other general taping applications. 3M Scotch Vinyl Mastic Tape is RoHS compliant.\*

VM tape is available in four sizes ranging from 1 ½" to 22" (38 mm-559 mm) in width to cover the majority of application needs in the field.



## Ordering Information

Part Number	Description	Stock Number	MOQ
VM-1.5x20	(1 ½" x 20') Vinyl Mastic Tape	80050045014	10
VM-22x10	(22" x 10') Vinyl Mastic Tape	80050045048	1
VM-4x10	(4" x 10') Vinyl Mastic Tape	80050045022	10
VM-6x10	(6" x 10') Vinyl Mastic Tape	80050045030	1

\*RoHS: compliant with EU RoHS Directive (2005/95/EC)

"RoHS Compliant 2005/95/EC" means that the product or part ("Product") does not contain any of the substances in excess of the maximum concentration values in EU Directive 2002/95/EC, as amended by Commission Decision 2005/618/EC, unless the substance is in an application that is exempt under RoHS. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

3M and Scotch are trademarks of 3M Company.

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



## Communication Markets Division

6801 River Place Blvd.  
Austin, TX 78726-9000  
800/695 0447  
Fax 800/626 0329  
www.3M.com/Telecom

Please recycle. Printed in U.S.A.  
© 3M 2010. All rights reserved.  
80-6113-8328-4

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Corning:

[VM-1.5X20](#) [VM-4X10](#) [VM-6X10](#) [VM-22X10](#)