


IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	150 Ω	260 Ω	410 Ω
Minimum	- Ω	208 Ω	- Ω



AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture, REF #3399

NOTES:

- CASE FLAMMABILITY RATING: UL94 V-0
- ASSEMBLED PART #: 28A3851-0A2
- CASE COLOR: -0A2 BLACK CASE.
- CORE DIMENSIONS REFER TO 28A3851-000 SPEC.
FERRITE CORE DIMENSION IS FOR INTERNAL PURPOSE
TO ENHANCE FITTING TO CASE AND ELECTRICAL
CHARACTERISTICS ONLY.
- COSMETIC SPECIFICATION REFER TO WI-QA-038.

CASE DIMENSIONS:

A	30.00 [1.181]	+	1.00 [.039]
B	13.00 [.512]	+	1.00 [.039]
C	33.70 [1.327]	+	1.00 [.039]
C1	38.90 [1.531]	+	1.50 [.059]
D	30.00 [1.181]	+	1.00 [.039]

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.		Laird™		
K	UPDATE CASE DIMENSIONS REMOVE CORE DIM AND ADD NOTE 4&5	01/13/14	Jcai					
J	REVISE NOTES ADD UL94 V-0 FLAMMABILITY UPDATE COMPANY LOGO	05/05/08	TMB					
H	UPDATE Z SPECS	06/27/07	JRK	PROJECT/PART NUMBER:		REV	PART TYPE:	DRAWN BY:
G	UPDATE COMPANY LOGO	04/19/07	TMB	28A3851-0A2		K	FERRITE SNAP-ON	JRK
F	REMOVE (SPEC) mm [in] FROM CORE & CASE DIMENSION VIEWS REMOVE CORE & CASE P/Ns FROM VIEWS UPDATE NOTES	03/21/07	TMB	DATE: 06/29/04		SCALE: NTS	MATERIAL:	
REV	DESCRIPTION	DATE	INT	CAD # 28A3851-0A2-K		TOOL # -	FERRITE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[28A3851-0A2](#)