


NOTES:

1. CORE: HP1040-2B0.
2. ADHESIVE: P/N 21228.
3. REFERENCE 3M TAPE 468MP ADHESIVE TRANSFER TAPE OR ENGINEER APPROVED ALTERNATIVE.
4. Cosmetic specification refer to WI-QA-038.

DIMENSIONS:

A	26.42 [1.040]	±	0.38 [.015]
B	26.42 [1.040]	±	0.38 [.015]
C	1.91 [.075]	±	0.13 [.005]
D	0.13 [.005]		TYP.
E	21.97 [.865]		TYP.

WEIGHT/1000 6.55 kgs [14.43 Lbs]

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.							
				PROJECT/PART NUMBER:		REV	PART TYPE:	DRAWN BY:			
				HP1040-200		K	FERRITE PLATE	JRK			
K	UPDATED LOGO, ADD NOTES 4		03/15/2019	Jcai	DATE:	09/24/02		SCALE:	2 : 1		MATERIAL: Ferrite
J	CHANGE D DIMENSION		7/10/09	JRK	CAD #	HP1040-200-K		TOOL #	P1040		
REV	DESCRIPTION		DATE	INT							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Laird Performance Materials:](#)

[HP1040-200](#)