


PAR	ΓNO.				
RMS-01 NATURAL	RMS-01 BLACK	"D" HOLDING DIA.	"E" REF.		
N-1	N-1-BK	N-1-BK 1/16 [1.6]			
N-2	N-2-BK	1/8 [3.2]	21/64 [8.3]		
N-3	N-3-BK	3/16 [4.8]	25/64 [9.9]		
N-4	N-4-BK	1/4 [6.4]	27/64 [10.7]		
N-5	N-5-BK	5/16 [7.9]	29/64 [11.5]		
N-6	N-6-BK	3/8 [9.5]	31/64 [12.3]		
N-7	N-7-BK	7/16 [11.1]	17/32 [13.5]		
N-8	N-8-BK	1/2 [12.7]	9/16 [14.3]		



SHOWN AS MOLDED

NOTES:

- 1. MATERIAL: NYLON 6/6 UL 94 V-0 (RMS-19).COLOR NATURAL, AVAILABLE BY SPECIAL ORDER ONLY.
- TO ORDER ADD "-19" TO THE END OF PART NUMBER.

 2. MATERIAL: NYLON 6/6 UL 94 V-2, UV STABILIZED (RMS-46), COLOR BLACK, AVAILABLE BY SPECIAL ORDER ONLY. TO ORDER REPLACE "-BK" WITH "-UVB"
- 3. RECOMMENDED SCREW SIZE IS #8 [M4], (#4 [M2.5] FOR N-1).

			CABLE CLAMP, N SERIES					DWG IN IN [MM]				
		CREATED USING SOLIDWORKS	FILE #: N-SERIES		DWN: S.K.	APP: R.G.	FINAL					
				TOLERANCES UNLESS NOTED	SHEET: 1	OF 1	SHEET SIZE: A	DT: 04/01/08	CHKD: S.J.	PART#		PRINT TYPE
G	SEE CO 200152 FOR CHANGES	SK (04/03/08	.XX=±.010 .XXX=±.005	RE: RICHCO, INC.		RICHCO, INC.		CEE T		TYPE	
-	SEE ENGINEERING FOR REV A-F	-		FRAC.=±1/64	, ,					ADLE	(CA)	
REV.	DESCRIPTION	ENGR.	DATE	ANG.=±1°				(773) 5	39-4060			O / \

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

<u>N-4</u> <u>N-5</u> <u>N-6</u> <u>N-7</u> <u>N-8</u> <u>N-1</u> <u>N-2</u> <u>N-3</u> <u>N-1</u> <u>N-2</u> <u>N-3</u> <u>N-7-BK</u> <u>N-1-BK</u> <u>N-2-BK</u> <u>N-2-BK</u> <u>N-3-BK</u> <u>N-4-BK</u> <u>N-5-BK</u> <u>N-6-BK</u> <u>N-8-BK</u> <u>N-8-BK</u> <u>N-7-19</u> <u>N-8-19</u> <u>N-1-19</u>