


Material: UL94 V-2 Nylon 6/6		
Color: Natural		
Part No.	A	
	mm	in
CBRLDS405A	2.5	.098
CBRLDS410A	3.2	.126
CBRLDS415A	4	.157
CBRLDS420A	5	.197
CBRLDS425A	6	.236
CBRLDS430A	7	.276
CBRLDS435A	8	.315
CBRLDS440A	9	.354
CBRLDS445A	10	.394
CBRLDS450A	12	.472
CBRLDS455A	14	.551
CBRLDS460A	16	.630

TO SNAP LOCK IN A 3 (.118) Ø HOLE, IN A
1.6 (.062) PANEL THICKNESS



TO SNAP LOCK IN A 4 (.157) Ø HOLE, IN A
0.8 - 1.6 (.031 - .062) PANEL THICKNESS

TOLERANCES
UNLESS NOTED

≤ 5 mm	±0.2
5 - 20 mm	±0.3
20 - 40 mm	±0.4
40 - 60 mm	±0.5
60 - 100 mm	±0.8
≥ 100 mm	±1.0

TITLE: DUAL LOCKING CIRCUIT BOARD SUPPORT		DWG IN MM (IN)	
FILE# CBR LDS4XX		PART #	
SHEET: 1 OF 1	SHEET SIZE: A	DT: 01/08/15	
RE:			PRINT TYPE CA
		SEE TABLE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[CBRLDS435A](#) [CBRLDS440A](#) [CBRLDS450A](#) [CBRLDS430A](#) [CBRLDS415A](#) [CBRLDS425A](#) [CBRLDS455A](#)
[CBRLDS410A](#) [CBRLDS445A](#) [CBRLDS460A](#) [CBRLDS420A](#) [CBRLDS405A](#)