





MBRR1-01



MBRP1-XXX-01 (SEE TABLE)



PART NO.	"L" ±.010	MAXIMUM PANEL THICKNESS
MBRP1-030-01	.133 [3.4]	.030 [0.8]
MBRP1-062-01	.165 [4.2]	.062 [1.6]
MBRP1-100-01	.203 [5.2]	.100 [2.5]
MBRP1-125-01	.228 [5.8]	.125 [3.2]
MBRP1-187-01	.290 [7.4]	.187 [3.2]
MBRP1-250-01	.353 [9]	.250 [6.4]
MBRR1-01	SEE DRAWING	

NOTES:
1. MATERIAL: NYLON 6/6 UL94 V-2 (RMS-01)
2. COLOR: NATURAL

D	CHANGED TOLERANCE ON "L" DIM, ECN # 1437	DZ	05/17/2018
C	REDRAWN, SEE CO 200766	SK	03/21/2012
-	SEE ENGINEERING FOR REV A TO B	--	-----
REV.	DESCRIPTION	ENGR.	DATE

TITLE: MINI BARBED RIVET						UNITS: IN [mm]	
CREATED USING SOLIDWORKS	FILE #: MBR		DWN: SK	APP: MB		FINAL	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1		SHEET SIZE: B		DT: 03/20/2012	CHKD: DZ	PART #
	RE: RICHCO, INC.		RICHCO, INC. WWW.RICHCO-INC.COM		SEE DRAWING		PRINT TYPE CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MBRP1-100-01](#) [MBRP1-030-01](#) [MBRP1-062-01](#) [MBRP1-125-01](#) [MBRP1-187-01](#) [MBRP1-250-01](#) [MBRR1-01](#)