


UNCONTROLLED DOCUMENT

NOTES:  
HOLE SIZE .355 / .355  
PANEL THICKNESS RANGE .062 / .350  
SCREW SIZE #10



TOLERANCES UNLESS NOTED

$\pm .005$  ON DIMENSIONS THRU .625  
 $\pm .008$  ON DIMENSIONS .626 THRU 1.000  
 $\pm .010$  ON DIMENSIONS 1.001 THRU 1.500  
 $\pm .015$  ON DIMENSIONS LARGER THAN 1.500  
 $\pm .015$  ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG DRAWING  
CLOSED GROMMET  
MICRO P/N 60SGN01402  
DWG. # 60SGN01402  
FILE SERVER\ENG\WEB

MATERIAL: NYLON 6/6

DATE

SCALE  
2:1

**DB**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[60SGN01402](#)