


UNCONTROLLED DOCUMENT



NOTES:  
.064 MINIMUM KEY ENGAGEMENT

TOLERANCES UNLESS NOTED

- ±.005 ON DIMENSIONS THRU .625
- ±.008 ON DIMENSIONS .626 THRU 1.000
- ±.010 ON DIMENSIONS 1.001 THRU 1.500
- ±.015 ON DIMENSIONS LARGER THAN 1.500
- ±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

|                                                                                                                     |              |           |
|---------------------------------------------------------------------------------------------------------------------|--------------|-----------|
| PROPERTY OF                                                                                                         |              |           |
| MICRO PLASTICS INC.                                                                                                 |              |           |
| CATALOG DRAWING<br>HEX SOCKET CAP MACHINE SCREW<br>MICRO P/N 3406320100<br>DWG. # 3406320100<br>FILE SERVER\ENG\WEB |              |           |
| MATERIAL:                                                                                                           |              | 6/6 NYLON |
| DATE                                                                                                                | SCALE<br>6:1 | JDD       |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[3406320100](#)