

UNCONTROLLED DOCUMENT

D

D

C

C

B

B

A

A

$\varnothing$  16.000  
15.670

5.00 MIN

10.000  
9.810

M10 X 1.5 THREADS

$\varnothing$  8.00 NOM

30.00 $\pm$ 0.4

ALL DIMENSIONS ARE IN MILLIMETERS  
TOLERANCES UNLESS NOTED

$\pm$ .13MM ON DIMENSIONS THRU 15.88MM  
 $\pm$ .20MM ON DIMENSIONS 15.89MM THRU 25.41MM  
 $\pm$ .25MM ON DIMENSIONS 25.42MM THRU 38.10MM  
 $\pm$ .38MM ON DIMENSIONS LARGER THAN 38.10MM

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG DRAWING  
HEX SOCKET HEAD CAP MACHINE SCREW  
MICRO P/N 50M100150S030  
DWG. # 50M100150S030  
FILE SERVER\ENG\WEB

MATERIAL: 6/6 NYLON

DATE

SCALE  
3:1

TA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[50M100150S030](#)