



# UNCONTROLLED DOCUMENT



NOTES:  
 HEAD STYLE - TRUSS  
 DRIVE PIN - ACETAL  
 ANCHOR RIVET - HIGH IMPACT MODIFIED NYLON TYPE 6/6

## TOLERANCES UNLESS NOTED

±.005 ON DIMENSIONS THRU .625  
 ±.008 ON DIMENSIONS .626 THRU 1.000  
 ±.010 ON DIMENSIONS 1.001 THRU 1.500  
 ±.015 ON DIMENSIONS LARGER THAN 1.500  
 ±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT  
 TO DISCONTINUE ITEMS,  
 CHANGE SPECIFICATIONS  
 OR DESIGN AT ANY TIME  
 WITHOUT NOTICE AND  
 WITHOUT INCURRING  
 ANY OBLIGATIONS

PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG DRAWING  
 TWO PIECE ANCHOR RIVET  
 MICRO P/N 61APT25125  
 DWG. # 61APT25125  
 FILE SERVER\ENG\WEB

MATERIAL: AS NOTED

DATE

SCALE  
 2:1

**TA**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[61APT25125](#)