



UNCONTROLLED DOCUMENT

Ø .625 REF



NOTES:  
HEAD STYLE - TRUSS  
DRIVE PIN - ACETAL  
ANCHOR RIVET - HIGH IMPACT MODIFIED NYLON TYPE 6/6

TOLERANCES UNLESS NOTED

±.005 ON DIMENSIONS THRU .625  
±.008 ON DIMENSIONS .626 THRU 1.000  
±.010 ON DIMENSIONS 1.001 THRU 1.500  
±.015 ON DIMENSIONS LARGER THAN 1.500  
±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG DRAWING  
TWO PIECE ANCHOR RIVET  
MICRO P/N 61APT25150  
DWG. # 61APT25150  
FILE SERVER\ENG\WEB

MATERIAL: SEE NOTES

DATE

SCALE  
2:1

**DSB**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[61APT25150](#)