


# UNCONTROLLED DOCUMENT



NOTES:  
HOLE SIZE - .156  
PANEL THICKNESS - .218 / .312  
HEAD STYLE - BINDER

## TOLERANCES UNLESS NOTED

$\pm .005$  ON DIMENSIONS THRU .625  
 $\pm .008$  ON DIMENSIONS .626 THRU 1.000  
 $\pm .010$  ON DIMENSIONS 1.001 THRU 1.500  
 $\pm .015$  ON DIMENSIONS LARGER THAN 1.500  
 $\pm .015$  ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

PROPERTY OF		
MICRO PLASTICS INC.		
CATALOG DRAWING POLY DRIVE RIVET MICRO P/N 61PR100300 DWG. # 61PR100300 FILE SERVER\ENG\WEB		
MATERIAL:		NYLON 6/6
DATE	SCALE 2:1	TA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[61PR100300](#)