




UNCONTROLLED DOCUMENT



TOLERANCES UNLESS NOTED

\pm .005 ON DIMENSIONS THRU .625
 \pm .008 ON DIMENSIONS .626 THRU 1.000
 \pm .010 ON DIMENSIONS 1.001 THRU 1.500
 \pm .015 ON DIMENSIONS LARGER THAN 1.500
 \pm .015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF
MICRO PLASTICS INC.

CATALOG DRAWING
82 DEGREE OVAL MACHINE SCREW
MICRO P/N 331024A050
DWG. # 331024A050
FILE SERVER\ENG\WEB

MATERIAL: 6/6 NYLON

DATE

SCALE
4:1

JDD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[331024A050](#)