

**UNCONTROLLED DOCUMENT**

Ø 4.40  
3.50

0.70  
0.50

1.00  
0.80

1.70 MAX

M2 X .4 THREADS

92°  
90°

1.20 MAX REF

8.00±0.3

ALL DIMENSIONS ARE IN MILLIMETERS  
TOLERANCES UNLESS NOTED

±.13MM ON DIMENSIONS THRU 15.88MM	<p>WE RESERVE THE RIGHT TO DISCONTINUE ITEMS, CHANGE SPECIFICATIONS OR DESIGN AT ANY TIME WITHOUT NOTICE AND WITHOUT INCURRING ANY OBLIGATIONS</p>	PROPERTY OF		
±.20MM ON DIMENSIONS 15.89MM THRU 25.41MM		MICRO PLASTICS INC.		
±.25MM ON DIMENSIONS 25.42MM THRU 38.10MM		<p>CATALOG DRAWING OVAL SLOTTED MACHINE SCREW MICRO P/N 50M020040L008 DWG. # 50M020040L008 FILE SERVER\ENG\WEB</p>		
±.38MM ON DIMENSIONS LARGER THAN 38.10MM		<p>MATERIAL: 6/6 NYLON</p>		
		DATE	SCALE 10:1	TA

ALL DIMENSIONS ARE IN MILLIMETERS  
TOLERANCES UNLESS NOTED

±.13MM ON DIMENSIONS THRU 15.88MM  
±.20MM ON DIMENSIONS 15.89MM THRU 25.41MM  
±.25MM ON DIMENSIONS 25.42MM THRU 38.10MM  
±.38MM ON DIMENSIONS LARGER THAN 38.10MM

WE RESERVE THE RIGHT  
TO DISCONTINUE ITEMS,  
CHANGE SPECIFICATIONS  
OR DESIGN AT ANY TIME  
WITHOUT NOTICE AND  
WITHOUT INCURRING  
ANY OBLIGATIONS

PROPERTY OF  
MICRO PLASTICS INC.

CATALOG DRAWING  
OVAL SLOTTED MACHINE SCREW  
MICRO P/N 50M020040L008  
DWG. # 50M020040L008  
FILE SERVER\ENG\WEB

MATERIAL: 6/6 NYLON

DATE \_\_\_\_\_

SCALE  
10:1

*TA*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[50M020040L008](#)