

Technical drawing of a mechanical part, showing front and side views with dimensions.

Front View (Left):

- Overall diameter: $\phi 5.50$
- Inner diameter: $\phi 4.40$
- Top radius: 0.80
- Bottom radius: 0.60

Side View (Right):

- Top thickness: 1.20
- Bottom thickness: 1.00
- Top width: 2.10 MAX
- Bottom width: 1.50 MAX REF
- Thread specification: $M2.5 \times .45 \text{ THREADS}$
- Thread length: 4.00 ± 0.3
- Angles: 92° and 90°

±.13MM	ON DIMENSIONS THRU 15.88MM
±.20MM	ON DIMENSIONS 15.89MM THRU 25.41MM
±.25MM	ON DIMENSIONS 25.42MM THRU 38.10MM
±.38MM	ON DIMENSIONS LARGER THAN 38.10MM

PROPERTY OF MICRO PLASTICS INC.

CATALOG DRAWING
OVAL SLOTTED MACHINE SCREW
MICRO P/N 50M025045L004
DWG. # 50M025045L004
FILE SERVER\ENG\WEB

MATERIAL: 6/6 NYLON

DATE _____

SCALE
8:1

TA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

50M025045L004