

UNCONTROLLED DOCUMENT

Ø 9.40
8.00

1.50
1.20

1.90
1.60

3.70 MAX

M4 X .7 THREADS

92°
90°

2.70 MAX REF

30.00±0.5

ALL DIMENSIONS ARE IN MILLIMETERS
TOLERANCES UNLESS NOTED

±.13MM ON DIMENSIONS THRU 15.88MM
±.20MM ON DIMENSIONS 15.89MM THRU 25.41MM
±.25MM ON DIMENSIONS 25.42MM THRU 38.10MM
±.38MM ON DIMENSIONS LARGER THAN 38.10MM

**WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS**

PROPERTY OF		
MICRO PLASTICS INC.		
CATALOG DRAWING OVAL SLOTTED MACHINE SCREW MICRO P/N 50M040070L030 DWG. # 50M040070L030 FILE SERVER\ENG\WEB		
MATERIAL:		6/6 NYLON
DATE	SCALE 4:1	TA

ALL DIMENSIONS ARE IN MILLIMETERS
TOLERANCES UNLESS NOTED

A

±.13MM ON DIMENSIONS THRU 15.88MM
±.20MM ON DIMENSIONS 15.89MM THRU 25.41MM
±.25MM ON DIMENSIONS 25.42MM THRU 38.10MM
±.38MM ON DIMENSIONS LARGER THAN 38.10MM

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

CATALOG DRAWING
OVAL SLOTTED MACHINE SCREW
MICRO P/N 50M040070L030
DWG. # 50M040070L030
FILE SERVER\ENG\WEB

DATE	SCALE 4:1	<i>TA</i>
------	--------------	-----------

TA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[50M040070L030](#)